

CRIMPFOX-TC MP - Crimping pliers with digital display



1212510

<https://www.phoenixcontact.com/us/products/1212510>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

Your advantages

- Crimping pliers for processing turned contacts of up to 2.5 mm²
- The integrated positioning tool ensures that the contacts are perfectly aligned
- Universal adjustment for precise processing of corresponding cross sections

Commercial data

Item number	1212510
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3135
GTIN	4046356555500
Weight per piece (including packing)	798.5 g
Weight per piece (excluding packing)	798.5 g
Customs tariff number	82032000
Country of origin	DE

CRIMPFOX-TC MP - Crimping pliers with digital display



1212510

<https://www.phoenixcontact.com/us/products/1212510>

Technical data

Notes

Note on application	The packing slip includes a detailed list of crimp contacts for turned crimp contacts of the series CC..., CUC...,
Utilization restriction	
EMC note	EMC: class A product, see manufacturer's declaration in the download area
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Four-mandrel crimping
Product property	Universal cross-section setting with digital display
	Electronic wear monitoring
	With positioning tool, replaceable
	For various Phoenix Contact contacts – see technical documentation
	Unlockable pressure lock

Crimping position 1

Min. cross section	0.08 mm ²
Max. cross section	2.5 mm ²
AWG min	28
AWG max	14

Connection data

Conductor connection

Cross section range, metric	0.08 mm ² ... 2.5 mm ²
Cross section range AWG	28 ... 14

Dimensions

Length	175 mm
--------	--------

Material specifications

Color	black/green
-------	-------------

CRIMPFOX-TC MP - Crimping pliers with digital display



1212510

<https://www.phoenixcontact.com/us/products/1212510>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212510>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-TC MP - Crimping pliers with digital display



1212510

<https://www.phoenixcontact.com/us/products/1212510>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-TC MP - Crimping pliers with digital display



1212510

<https://www.phoenixcontact.com/us/products/1212510>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)(CAS: 110-71-4)
	Lead(CAS: 7439-92-1)
SCIP	e67f1777-45c4-4f95-8d9b-644aca75c585

EF3.1 Climate Change

CO2e kg	117.157 kg CO2e
---------	-----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com