

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, compact pliers, coaxial connectors, 0.7 mm, 1.07 mm, 1.69 mm, 3.25 mm, 4.52 mm, 5.41 mm, six marked die stations, unlockable pressure lock, lateral entry, hex crimp

The figure shows a version of the article

Your advantages

- Lateral conductor entry
- Unlockable pressure lock
- Crimping pliers for processing coaxial connectors

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212712 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3138 |
| GTIN | 4046356857611 |
| Weight per piece (including packing) | 618.3 g |
| Weight per piece (excluding packing) | 618.3 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|------------------|---|
| Product type | Crimping tool |
| Compression | HEX crimp |
| Product property | Lateral conductor entry |
| | Unlockable pressure lock |
| | Crimping pliers for processing coaxial connectors |

Crimping position 1

Crimping width 3.25 mm

Crimping position 2

Crimping width 4.52 mm

Crimping position 3

Crimping width 5.41 mm

Crimping position 4

Crimping width 1.69 mm

Crimping position 5

Crimping width 1.07 mm

Crimping position 6

Max. cross section 0.7 mm²

Connection data

Conductor connection

Cross section range, metric 0.72 mm² ... 5.41 mm²

Dimensions

| | |
|--------|--------|
| Width | 22 mm |
| Height | 76 mm |
| Length | 204 mm |

External dimensions

Outside diameter 0.72 mm ... 5.41 mm

Material specifications

Color black

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212712>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-CX 5,41-M - Crimping pliers



1212712

<https://www.phoenixcontact.com/us/products/1212712>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com