

SAC-8P-10,0-850/M12FS HN - Sensor/actuator cable



1402580

<https://www.phoenixcontact.com/us/products/1402580>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PUR halogen-free, black RAL 9005, shielded, free cable end, on Socket straight M12, coding: A, cable length: 10 m, Customer version, with hybrid cable

As in the figure but with black grip and hybrid cable

Commercial data

Item number	1402580
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	AF1CMA
GTIN	4046356624053
Weight per piece (including packing)	556.2 g
Weight per piece (excluding packing)	556.2 g
Country of origin	PL

1402580

<https://www.phoenixcontact.com/us/products/1402580>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	8
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	2 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Connector

Connection 1

Type	free cable end
------	----------------

SAC-8P-10,0-850/M12FS HN - Sensor/actuator cable



1402580

<https://www.phoenixcontact.com/us/products/1402580>

Connection 2

Type	Socket straight M12
Number of positions	8
Coding type	A

Cable/line

Cable length	10 m
--------------	------

PUR halogen-free black [850]

Number of positions	8
Shielded	yes
Cable type	PUR halogen-free black [850]
Conductor structure signal line	19x 0.10 mm
AWG signal line	26
Conductor structure, voltage supply	45x 0.10 mm
AWG power supply	22
Conductor cross-section	4x 0.14 mm ² (Signal line) 4x 0.34 mm ² (Power supply)
Wire diameter incl. insulation	1 mm (Signal line) 1.1 mm (Power supply)
External cable diameter	6 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material, filler	PE + filler yarn
Material wire insulation	Foamed PE (Signal line) TPE (Power supply)
Single wire, color	yellow, gray, violet, pink, white-green, brown-green, white, blue
Thickness, insulation	≥ 0.38 mm (Outer cable sheath)
Optical shield covering	85 %
Max. conductor resistance	≤ 134 mΩ/m (Signal line) ≤ 55 mΩ/m (Power supply)
Insulation resistance	> 200 MΩ*km
Working capacitance	≤ 40 pF (Signal line)
Nominal voltage, cable	30 V
Test voltage Core/Core	500 V AC (at 50 Hz)
Test voltage Core/Shield	500.00 V AC (at 50 Hz)
Smallest bending radius, fixed installation	≥ 20 mm
Smallest bending radius, movable installation	≥ 75 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 75 mm
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-8P-10,0-850/M12FS HN - Sensor/actuator cable



1402580

<https://www.phoenixcontact.com/us/products/1402580>

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

SAC-8P-10,0-850/M12FS HN - Sensor/actuator cable



1402580

<https://www.phoenixcontact.com/us/products/1402580>

Circuit diagram



Contact assignment of the M12 socket

SAC-8P-10,0-850/M12FS HN - Sensor/actuator cable



1402580

<https://www.phoenixcontact.com/us/products/1402580>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

1402580

<https://www.phoenixcontact.com/us/products/1402580>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com