

NBC-M12MSD/25,0-937/M12MRD - Network cable



1407985

<https://www.phoenixcontact.com/us/products/1407985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled PROFINET cable, CAT5e, shielded, star quad, 22 AWG stranded (7-wire), black, straight M12 plug to angled M12 plug, line, length: 25 m

Commercial data

Item number	1407985
Packing unit	1 pc
Minimum order quantity	25 pc
Product key	AF1CJN
GTIN	4046356787772
Weight per piece (including packing)	1,730.7 g
Weight per piece (excluding packing)	1,696.75 g
Country of origin	PL

1407985

<https://www.phoenixcontact.com/us/products/1407985>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	PROFINET
Number of positions	4

Interfaces

Bus system	PROFINET
Signal type/category	PROFINET

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Material specifications

Outer sheath, material	PE-X
------------------------	------

Connector

Connection 1

Type	Plug straight M12
Coding type	D (Data)

Connection 2

Type	Plug angled M12
Coding type	D (Data)

Cable/line

Cable length	25 m
Signal type/category	PROFINET
Outer sheath, material	PE-X
External sheath, color	black RAL 9005

NBC-M12MSD/25,0-937/M12MRD - Network cable



1407985

<https://www.phoenixcontact.com/us/products/1407985>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com