# HC-B 24-TFQ-H-O1STM32S - Housing

1409367

https://www.phoenixcontact.com/us/products/1409367

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B24 sleeve housing, for double locking latch, height: 76 mm, with 1 x M32 thread, lateral cable outlet

## Commercial data

| | |
|---|---|
| Item number | 1409367 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BF55 |
| Product key | AF7AAC |
| GTIN | 4046356664233 |
| Weight per piece (including packing) | 249 g |
| Weight per piece (excluding packing) | 241 g |
| Customs tariff number | 79070000 |
| Country of origin | DE |

## Technical data


### Notes

| | |
|---|---|
| General | For contact inserts HC-B24, BB46, BBB64, D64, DD108, M |

### Product properties

| | |
|---|---|
| Product type | Housing with locking latch |
| Housing type | Sleeve housing |
| Application | Standard |
| Type | B24 |
| No. of cable outlets | 1 |
| Type of the screw connection | 1x M32 |
| Shielded | no |
| Cable outlet | lateral |
| Pg screw connection | none |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 43 mm |
| Height | 76 mm |
| Length | 120 mm |

### Material specifications

| | |
|---|---|
| Housing material | Die-cast aluminum |
| Housing surface material | Powder-coated, gray |

### Mechanical properties

Mechanical data

| | |
|---|---|
| Type of the screw connection | 1x M32 |
| Locking type | Pin |


### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP65 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

## Drawings

Dimensional drawing




Dimensional drawing

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261501 |

## Environmental product compliance

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com