

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, TPE, yellow, Plug straight M12 SPEEDCON, coding: A, on Socket straight M12 SPEEDCON, coding: A, cable length: 1.5 m

Commercial data

Item number	1410244
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF13
Product key	AF1IFA
GTIN	4055626048703
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	US

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard, U.S. cables
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	TPE

Electrical properties

Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	3
Locking type	SPEEDCON
Coding type	A

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>


Connection 2

Type	Socket straight M12 SPEEDCON
Number of positions	3
Locking type	SPEEDCON
Coding type	A

Cable/line

Cable length	1.5 m
--------------	-------

TPE yellow 105 °C [647]

Dimensional drawing	
Cable weight	23 kg/km
UL AWM Style	20327 (105 °C / 300 V)
Number of positions	3
Shielded	no
Cable type	TPE yellow 105 °C [647]
Conductor structure signal line	41x 0.16 mm
AWG signal line	18
Wire diameter incl. insulation	1.8 mm
External cable diameter	5.70 mm ±0.25 mm
Outer sheath, material	TPE
External sheath, color	yellow
Material wire insulation	PVC
Thickness, insulation	0.23 mm
Thickness, outer sheath	0.89 mm
Overall twist	3 wires, twisted
Nominal voltage, cable	300 V
Flame resistance	According to FT1
Resistance to oil	OIL RES I according to UL 2256
Other resistance	UV resistant (720 h) (to UL 2256)
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

	IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



M12 x 1 socket, straight

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SAC-3P-MS/1,5-647/FS SCO BK - Sensor/actuator cable



1410244

<https://www.phoenixcontact.com/us/products/1410244>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com