

CUC-V14-A3ST-SR - Panel-mount frame



1413990

<https://www.phoenixcontact.com/us/products/1413990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel-mount frame, degree of protection: IP65/IP67, material: Stainless steel

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1413990 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB17 |
| Product key | ABNODZ |
| GTIN | 4055626082370 |
| Weight per piece (including packing) | 14.4 g |
| Weight per piece (excluding packing) | 14.4 g |
| Customs tariff number | 73269098 |
| Country of origin | DE |

CUC-V14-A3ST-SR - Panel-mount frame



1413990

<https://www.phoenixcontact.com/us/products/1413990>

Technical data

Product properties

| | |
|--------------|-------------------|
| Product type | Panel-mount frame |
| Type | Version 14 |

Insulation characteristics

| | |
|---------------------|---|
| Degree of pollution | 2 |
|---------------------|---|

Dimensions

| | |
|--------|---------|
| Width | 22 mm |
| Height | 17 mm |
| Length | 68.6 mm |

Material specifications

| | |
|--|-----------------|
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |
| Housing material | Stainless steel |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP65/IP67 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 55 °C |

CUC-V14-A3ST-SR - Panel-mount frame



1413990

<https://www.phoenixcontact.com/us/products/1413990>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121421 |
|-------------|----------|

CUC-V14-A3ST-SR - Panel-mount frame



1413990

<https://www.phoenixcontact.com/us/products/1413990>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com