

# HC-B-TA-NPT-1/1-PLR-BK - Adapter



1414253

<https://www.phoenixcontact.com/us/products/1414253>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic thread adapter with bayonet lock, for EVO housing series B, NPT 1/1" thread



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1414253       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF57          |
| Product key                          | AF7APL        |
| GTIN                                 | 4055626022161 |
| Weight per piece (including packing) | 25.3 g        |
| Weight per piece (excluding packing) | 24.3 g        |
| Customs tariff number                | 85389099      |
| Country of origin                    | PL            |

# HC-B-TA-NPT-1/1-PLR-BK - Adapter

1414253

<https://www.phoenixcontact.com/us/products/1414253>

## Technical data


### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Thread adapter  |
| Application  | Bayonet B - NPT |
| Shielded     | no              |

### Connection data

|                   |           |
|-------------------|-----------|
| Tightening torque | ... 12 Nm |
|-------------------|-----------|

### Dimensions

|                          |  |
|--------------------------|--|
| Dimensional drawing      |  |
| Thread type on seal side | 1"-NPT   |

### Internal dimensions

|                           |       |
|---------------------------|-------|
| Length of internal thread | 15 mm |
|---------------------------|-------|

### Material specifications

|  |     |
|--|-----|
| Flammability rating according to UL 94 | V0  |
| Seal material                          | NBR |
| Housing material                       | PA  |

### Cable/line

|                         |                              |
|-------------------------|------------------------------|
| External cable diameter | depending on the cable gland |
|-------------------------|------------------------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP66              |
| Ambient temperature (operation) | -40 °C ... 100 °C |

### Mounting

|               |   |
|---------------|---|
| Assembly note | Bayonet locking max. 3x can be removed<br>The plastic thread adapter does not establish an electrical connection between the cable gland and connector housing. For this reason, only plastic cable protection systems or plastic cable glands may be used. |
|---------------|---|

# HC-B-TA-NPT-1/1-PLR-BK - Adapter





1414253

<https://www.phoenixcontact.com/us/products/1414253>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-B-TA-NPT-1/1-PLR-BK - Adapter



1414253

<https://www.phoenixcontact.com/us/products/1414253>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414253>

**DNV**

Approval ID: TAE000037S



**cUL Recognized**

Approval ID: E255026



**UL Recognized**

Approval ID: E255026



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# HC-B-TA-NPT-1/1-PLR-BK - Adapter



1414253

<https://www.phoenixcontact.com/us/products/1414253>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140801 |
| ECLASS-15.0 | 27140801 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000441 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# HC-B-TA-NPT-1/1-PLR-BK - Adapter



1414253

<https://www.phoenixcontact.com/us/products/1414253>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.281 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)