

# CUC-DSC-C1BAU-S/DSC22 - D-SUB crimp contact



1418789

<https://www.phoenixcontact.com/us/products/1418789>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB crimp contact, Pin, turned, contact diameter: 0.76 mm, rated current: 3 A, connection cross section: 0.08 mm<sup>2</sup> ... 0.34 mm<sup>2</sup>, AWG 28...22, contact material: Metal

## Product description

High-density contact for D-SUB contact inserts

## Your advantages

- High grade
- Various connection methods for every application
- Turned contact

## Commercial data

Item number	1418789
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB19
Product key	ABNCAC
GTIN	4055626150765
Weight per piece (including packing)	0.101 g
Weight per piece (excluding packing)	0.07 g
Customs tariff number	85366990
Country of origin	CH

1418789

<https://www.phoenixcontact.com/us/products/1418789>

## Technical data

### Mounting

Mounting type	Crimp connection
---------------	------------------

### Product properties

Product type	Crimp contact
Contact material type	turned

### Connection data

#### Connection technology

Contact connection type	Pin
Connection method	Crimp connection

#### Conductor connection

Connection cross section	0.08 mm <sup>2</sup> ... 0.34 mm <sup>2</sup>
Connection cross section AWG	28 ... 22

### Material specifications

Material Contact	Metal
Material Plug contact coating (top layer/selective)	Au (0.2 µm)
Material	Ni
Material Contact	Brass

### Dimensions

Width [w]	1.2 mm
Height [h]	1.2 mm
Length [l]	13.38 mm
Diameter (Contact diameter)	0.76 mm

### Electrical properties

Rated current (Maximum load current)	3 A
--------------------------------------	-----

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 200
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 115 °C
---------------------------------	-------------------

# CUC-DSC-C1BAU-S/DSC22 - D-SUB crimp contact



1418789

<https://www.phoenixcontact.com/us/products/1418789>

## Classifications

### ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

1418789

<https://www.phoenixcontact.com/us/products/1418789>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	256e2644-582e-4521-b12e-a1bc07480765

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)