

# HC-B 10-TFL-N-O1STM25G - Housing

1460039

<https://www.phoenixcontact.com/us/products/1460039>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B10 sleeve housing, for single locking latch, height: 56 mm, with 1 x M25 thread, straight cable outlet

## Commercial data

Item number	1460039
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAC
GTIN	4046356695534
Weight per piece (including packing)	148 g
Weight per piece (excluding packing)	131 g
Customs tariff number	85389099
Country of origin	DE

# HC-B 10-TFL-N-O1STM25G - Housing

1460039


<https://www.phoenixcontact.com/us/products/1460039>

## Technical data

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B10
No. of cable outlets	1
Type of the screw connection	1x M25
Shielded	no
Cable outlet	straight
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	43 mm
Height	56 mm
Length	73 mm

### Material specifications

Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M25
Locking type	Pin

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B 10-TFL-N-O1STM25G - Housing




1460039

<https://www.phoenixcontact.com/us/products/1460039>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 10-TFL-N-O1STM25G - Housing



1460039

<https://www.phoenixcontact.com/us/products/1460039>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# HC-B 10-TFL-N-O1STM25G - Housing



1460039

<https://www.phoenixcontact.com/us/products/1460039>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)