

# HC-B 16-TFQ-H-M1PG21G - Housing

1460139

<https://www.phoenixcontact.com/us/products/1460139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B16 sleeve housing, for double locking latch, height: 76 mm, with 1 x Pg21 screw connection, straight cable outlet

## Commercial data

Item number	1460139
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAC
GTIN	4046356793872
Weight per piece (including packing)	248.84 g
Weight per piece (excluding packing)	235.7 g
Customs tariff number	85389099
Country of origin	DE

# HC-B 16-TFQ-H-M1PG21G - Housing

1460139

<https://www.phoenixcontact.com/us/products/1460139>

## Technical data


### Notes

General	For contact inserts HC-B16, BB32, BBB40, D40, DD72, HS6, M, K
---------	---------------------------------------------------------------

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Type	B16
No. of cable outlets	1
Type of the screw connection	1x Pg21
Cable outlet	straight
Pg screw connection	with

### Dimensions

Dimensional drawing	
Width	43 mm
Height	76 mm
Length	94 mm
Wrench size, union nut	28 mm

### Material specifications

Material Screw connection	Brass, nickel-plated
Seal material Cable seal	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x Pg21
------------------------------	---------

### Cable/line

External cable diameter	10 mm ... 19 mm
-------------------------	-----------------

### Connection data

External cable diameter	10 mm ... 19 mm
-------------------------	-----------------

### Environmental and real-life conditions

# HC-B 16-TFQ-H-M1PG21G - Housing



1460139

<https://www.phoenixcontact.com/us/products/1460139>

## Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B 16-TFQ-H-M1PG21G - Housing




1460139

<https://www.phoenixcontact.com/us/products/1460139>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 16-TFQ-H-M1PG21G - Housing



1460139

<https://www.phoenixcontact.com/us/products/1460139>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# HC-B 16-TFQ-H-M1PG21G - Housing



1460139

<https://www.phoenixcontact.com/us/products/1460139>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)