

# HC-B 48-TFL-96/O1STM50G - Housing



1460337

<https://www.phoenixcontact.com/us/products/1460337>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON sleeve housing B48, for single locking latch, height 96 mm, with thread 1x M50, straight conductor exit

## Commercial data

Item number	1460337
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAC
GTIN	4046356696562
Weight per piece (including packing)	675.1 g
Weight per piece (excluding packing)	675.1 g
Customs tariff number	85389099
Country of origin	DE

# HC-B 48-TFL-96/O1STM50G - Housing

1460337


<https://www.phoenixcontact.com/us/products/1460337>

## Technical data

### Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Type	B48
No. of cable outlets	1
Type of the screw connection	1x M50
Cable outlet	straight
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	89 mm
Height	96 mm
Length	131.5 mm

### Material specifications

Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

### Mechanical properties

#### Mechanical data

Type of the screw connection	1x M50
Locking type	Pin

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B 48-TFL-96/O1STM50G - Housing




1460337

<https://www.phoenixcontact.com/us/products/1460337>

## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 48-TFL-96/O1STM50G - Housing



1460337

<https://www.phoenixcontact.com/us/products/1460337>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# HC-B 48-TFL-96/O1STM50G - Housing



1460337

<https://www.phoenixcontact.com/us/products/1460337>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)