

SACB- 4/3-L-M12-M8 - Distributor box



1516234

<https://www.phoenixcontact.com/us/products/1516234>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Standard, connection method: M8 socket Metal, number of slots: 4, number of positions: 3, coding: A, slot assignment: single, status display: yes, PNP; master cable connection: M12 plug connection 90°, shielding: no

Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Convenient: increased machine availability thanks to quick and easy diagnostics

Commercial data

Item number	1516234
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF40
Product key	AF3BCB
GTIN	4017918967161
Weight per piece (including packing)	92.9 g
Weight per piece (excluding packing)	91.7 g
Customs tariff number	85366990
Country of origin	PL

SACB- 4/3-L-M12-M8 - Distributor box



1516234

<https://www.phoenixcontact.com/us/products/1516234>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

Product properties

Product type	Distributor box
Application	Standard
Number of positions	3
Number of slots	4
Coding	A
LED	yes

System properties

Local diagnostics

Monitored function	Supply voltage per module
Optical representation	Green LED

Electrical properties

Max. operating voltage U_{max}	30 V DC
Local diagnostics	Supply voltage per module Green LED
	Status display I/O Yellow LED
Nominal voltage U_N	24 V DC
Rated current, total	4 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	2 A

Connection data

Conductor connection

Sensor/actuator connection system	M8 socket
Tightening torque slot sensor/actuator cable	0.2 Nm
Tightening torque - master cable - plug connection	0.4 Nm

Connection assignment

Slot/position = Wire color or connection	1 / 4 (A) = 1
	2 / 4 (A) = 2
	3 / 4 (A) = 3
	4 / 4 (A) = 4
	1-4 / 1 (+ 24 V) = 5

SACB- 4/3-L-M12-M8 - Distributor box



1516234

<https://www.phoenixcontact.com/us/products/1516234>


1-4 / 3 (0 V) = 7

Signaling

Status display present yes

Dimensions

Dimensional drawing



Width	30 mm
Height	27 mm
Length	93 mm

Material specifications

Material Threaded sleeve	Cu alloy
Material Housing	PBT
Material Molding compound	PUR
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of contact, master cable side	CU alloy
Material of contact surface, master cable side	gold-plated

Cable/line

Connection method M12 plug connection

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-30 °C ... 80 °C

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

M8

Standard designation	M8 connector
----------------------	--------------

SACB- 4/3-L-M12-M8 - Distributor box



1516234

<https://www.phoenixcontact.com/us/products/1516234>

Standards/specifications

IEC 61076-2-104


SACB- 4/3-L-M12-M8 - Distributor box

1516234


<https://www.phoenixcontact.com/us/products/1516234>

Drawings

Dimensional drawing



Schematic diagram



Pin assignment M8 socket, 3-pos.

SACB- 4/3-L-M12-M8 - Distributor box

1516234

<https://www.phoenixcontact.com/us/products/1516234>

Schematic diagram



Connector pin assignment for M12 plug-in connection, 8-pos.

Circuit diagram



Further information can be found in the connection assignment section

SACB- 4/3-L-M12-M8 - Distributor box



1516234

<https://www.phoenixcontact.com/us/products/1516234>

Classifications

ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SACB- 4/3-L-M12-M8 - Distributor box



1516234

<https://www.phoenixcontact.com/us/products/1516234>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com