


SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR/PVC, black-gray RAL 7021, free cable end, on Socket straight 1/2"-20UNF, coding: C, cable length: 5 m

Commercial data

Item number	1527016
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF09
Product key	AF1EBA
GTIN	4046356071840
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Customs tariff number	85444290
Country of origin	US

SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Technical data

Notes

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	C

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 10 \text{ M}\Omega$
Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight 1/2"-20UNF
Number of positions	3

SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016


<https://www.phoenixcontact.com/us/products/1527016>

Coding type	C
-------------	---

Cable/line

Cable length	5 m
--------------	-----

PUR/PVC black [350]

Dimensional drawing	
Cable weight	37 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR/PVC black [350]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	0.34 mm ²
Wire diameter incl. insulation	1.5 mm ±0.05 mm
External cable diameter	5.20 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	green, red-black, red-white
Thickness, insulation	approx. 0.30 mm (Core insulation) ≥ 0.38 mm (Outer cable sheath)
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≤ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	52 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 52 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Flame resistance	in accordance with DIN UL-Style 20549
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable

1527016

<https://www.phoenixcontact.com/us/products/1527016>


Drawings

Dimensional drawing



1/2"-20UNF socket, straight

Schematic diagram



Pin assignment 1/2"-20UNF socket, 2-pos., view female side


SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Circuit diagram



Contact assignment of 1/2" UNF plugs / sockets

SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1527016>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	4 A	-	-

SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

SAC-3P-MICFS/ 5,0-PUR - Sensor/actuator cable



1527016

<https://www.phoenixcontact.com/us/products/1527016>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com