

HC-B 6-KML-52/O1M20 - Housing



1604719

<https://www.phoenixcontact.com/us/products/1604719>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON coupling housing B6, with single locking latch, height 73 mm, with support 1x M20



Commercial data

Item number	1604719
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF7AAC
GTIN	4017918881634
Weight per piece (including packing)	205.59 g
Weight per piece (excluding packing)	205.59 g
Customs tariff number	85389099
Country of origin	DE

HC-B 6-KML-52/O1M20 - Housing

1604719

<https://www.phoenixcontact.com/us/products/1604719>

Technical data


Notes

General	For contact inserts HC-B6, BB10, DD24, M
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Coupling housings
Application	Standard
Type	B6
No. of cable outlets	1
Type of the screw connection	1x M20
Cable outlet	straight

Dimensions

Dimensional drawing	
Width	43 mm
Height	73 mm
Length	60 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Locking latch material	High-grade steel, handle: PA-GF

Mechanical properties

Mechanical data

Type of the screw connection	1x M20
------------------------------	--------

Mounting

Assembly note	For half and full screw connections
---------------	-------------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

HC-B 6-KML-52/O1M20 - Housing


1604719

<https://www.phoenixcontact.com/us/products/1604719>



Drawings

Dimensional drawing



HC-B 6-KML-52/O1M20 - Housing



1604719

<https://www.phoenixcontact.com/us/products/1604719>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

1604719

<https://www.phoenixcontact.com/us/products/1604719>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com