

# SF-10KP360 - Crimp contact



1615964

<https://www.phoenixcontact.com/us/products/1615964>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: SF, Pin, rolled

## Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring
- Variable production run startup, thanks to full or semi-automation

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1615964                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AB38                           |
| Product key                          | ABRECE                         |
| GTIN                                 | 4046356574747                  |
| Weight per piece (including packing) | 3,650 g                        |
| Weight per piece (excluding packing) | 3,650 g                        |
| Customs tariff number                | 85389099                       |
| Country of origin                    | DE                             |

# SF-10KP360 - Crimp contact



1615964

<https://www.phoenixcontact.com/us/products/1615964>

## Technical data

### Product properties

|                       |               |
|-----------------------|---------------|
| Product type          | Crimp contact |
| Series                | SF            |
| Contact material type | rolled        |

### Connection data

#### Connection technology

|                         |     |
|-------------------------|-----|
| Contact connection type | Pin |
|-------------------------|-----|

### Mechanical properties

#### Mechanical data

|                             |     |
|-----------------------------|-----|
| Insertion/withdrawal cycles | 500 |
|-----------------------------|-----|

# SF-10KP360 - Crimp contact




1615964

<https://www.phoenixcontact.com/us/products/1615964>

## Drawings

Dimensional drawing



# SF-10KP360 - Crimp contact



1615964

<https://www.phoenixcontact.com/us/products/1615964>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)