

HC-D 25-TFL-72/O1STM25S - Housing



1645273

<https://www.phoenixcontact.com/us/products/1645273>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON sleeve housing D25, for single locking latch, height 72 mm, without support 1x M25, lateral conductor exit

Commercial data

Item number	1645273
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF55
Product key	AF7AAE
GTIN	4017918913106
Weight per piece (including packing)	199.58 g
Weight per piece (excluding packing)	199.58 g
Customs tariff number	85389099
Country of origin	DE

HC-D 25-TFL-72/O1STM25S - Housing

1645273

<https://www.phoenixcontact.com/us/products/1645273>

Technical data


Notes

General	For contact inserts HC-D25, A16
---------	---------------------------------

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	D25
No. of cable outlets	1
Type of the screw connection	1x M25
Shielded	no
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	36 mm
Height	72 mm
Length	79.5 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

Mechanical properties

Mechanical data

Type of the screw connection	1x M25
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

HC-D 25-TFL-72/O1STM25S - Housing




1645273

<https://www.phoenixcontact.com/us/products/1645273>

Drawings

Dimensional drawing



Dimensional drawing

HC-D 25-TFL-72/O1STM25S - Housing



1645273

<https://www.phoenixcontact.com/us/products/1645273>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

HC-D 25-TFL-72/O1STM25S - Housing



1645273

<https://www.phoenixcontact.com/us/products/1645273>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com