

# VS-09-T-20-1-S-S - D-SUB sleeve housings




1655658

<https://www.phoenixcontact.com/us/products/1655658>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB sleeve housings, design: D-SUB 9, degree of protection: IP20, material: ABS, cable outlet: straight, housing size: 1, color: Bare metallic



## Commercial data

Item number	1655658
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ABNCAE
GTIN	4046356029544
Weight per piece (including packing)	17.7 g
Weight per piece (excluding packing)	17 g
Customs tariff number	85389099
Country of origin	HU

# VS-09-T-20-1-S-S - D-SUB sleeve housings

1655658


<https://www.phoenixcontact.com/us/products/1655658>

## Technical data

### Product properties

Product type	Sleeve housings
Type	D-SUB 9
No. of cable outlets	1
Cable outlet	straight

### Dimensions

Dimensional drawing	
Width	31.2 mm
Height	38 mm
Length	15.2 mm

### Material specifications

Color	Bare metallic
Flammability rating according to UL 94	V0
Housing material	ABS
Housing surface material	Ni

### Cable/line

External cable diameter	4 mm ... 8.5 mm
-------------------------	-----------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

### Mounting

Mounting type	Screw locking mechanism
---------------	-------------------------


# VS-09-T-20-1-S-S - D-SUB sleeve housings

1655658

<https://www.phoenixcontact.com/us/products/1655658>

## Drawings

Dimensional drawing



# VS-09-T-20-1-S-S - D-SUB sleeve housings



1655658

<https://www.phoenixcontact.com/us/products/1655658>

## Classifications

### ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

# VS-09-T-20-1-S-S - D-SUB sleeve housings



1655658

<https://www.phoenixcontact.com/us/products/1655658>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)