

UHV -TP2 - Separating plate

2130415

<https://www.phoenixcontact.com/us/products/2130415>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Separating plate, width: 2 mm, height: 68.3 mm, color: gray



The figure shows the product version UHV-TP 1

Commercial data

Item number	2130415
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1ZWX
GTIN	4017918053147
Weight per piece (including packing)	24.34 g
Weight per piece (excluding packing)	22.98 g
Customs tariff number	85389099
Country of origin	IN

UHV -TP2 - Separating plate



2130415

<https://www.phoenixcontact.com/us/products/2130415>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Material specifications

Color	gray
Flammability rating according to UL 94	V2
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	2 mm
Height	68.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

UHV -TP2 - Separating plate

2130415

<https://www.phoenixcontact.com/us/products/2130415>



Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UHV -TP2 - Separating plate



2130415

<https://www.phoenixcontact.com/us/products/2130415>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com