

# UM-PRO A/U 92 L15,60CM - Covering hood



2201968

<https://www.phoenixcontact.com/us/products/2201968>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching, Cover, length: 156 mm, Note: max. length of the cover = PCB length - 19 mm



The figure shows the standard item

## Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

## Commercial data

Item number	2201968
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	ACHDBZ
GTIN	4046356947039
Weight per piece (including packing)	68.99 g
Weight per piece (excluding packing)	61.66 g
Customs tariff number	39269097
Country of origin	DE

# UM-PRO A/U 92 L15,60CM - Covering hood



2201968

<https://www.phoenixcontact.com/us/products/2201968>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	---

### Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM-PRO
Ventilation openings present	no

### Dimensions

Length	156 mm
--------	--------

### Material specifications

Color (Housing)	transparent
Material	PC

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

### Mounting

Mounting type	Latching
Mounting position	vertical or horizontal

### Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

# UM-PRO A/U 92 L15,60CM - Covering hood



2201968

<https://www.phoenixcontact.com/us/products/2201968>

## Classifications

### ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

### UNSPSC

UNSPSC 21.0	31261501
-------------	----------

# UM-PRO A/U 92 L15,60CM - Covering hood



2201968

<https://www.phoenixcontact.com/us/products/2201968>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)