

2202030

<https://www.phoenixcontact.com/us/products/2202030>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Locking element for locking the PCB onto UM-BASIC/PRO housing at level 3



Your advantages

- Different base profiles, each with three PCB levels
- Module covers of different geometries can be positioned in any way
- Compatibility with many standard connection technologies
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2202030
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC13
Product key	ACHDAZ
GTIN	4055626005416
Weight per piece (including packing)	0.306 g
Weight per piece (excluding packing)	0.3 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Mounting material
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM-BASIC
Product family	UM-PRO

Material specifications

Color (Housing)	light gray (RAL 7035)
Material Housing	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Plug-in mounting
---------------	------------------

UM-BASIC/PRO PCB C-LOCK L3KMGY - Locking



2202030

<https://www.phoenixcontact.com/us/products/2202030>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202030>



UL Recognized

Approval ID: E240868

2202030

<https://www.phoenixcontact.com/us/products/2202030>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-BASIC/PRO PCB C-LOCK L3KMGY - Locking



2202030

<https://www.phoenixcontact.com/us/products/2202030>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com