

# FLKM-I/O - Optocoupler module



2282075

<https://www.phoenixcontact.com/us/products/2282075>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Interface module, with plug-in socket for one solid-state relay with security latch, screw connection, light indicator and fuse. Control logic: minus switching.

## Your advantages

- Status indicator
- Integrated fuse for line protection
- Can be fitted with solid-state relays or I/O modules

## Commercial data

Item number	2282075
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61Y2
GTIN	4046356684910
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	US

# FLKM-I/O - Optocoupler module



2282075

<https://www.phoenixcontact.com/us/products/2282075>

## Technical data

### Notes

#### Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

### Product properties

Product type	Relay Module
--------------	--------------

### Input data

Typical input current at $U_N$	30 mA (Optocoupler dependent)
Status display/channel	Red LED

### Output data

#### Switching

Limiting continuous current	4 A
Error detection (line break / short-circuit)	no

### Connection data

#### Input

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of connections	1
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 14

### Dimensions

Width	45 mm
Height	77 mm
Depth	72 mm

### Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC, side panel PA non-reinforced,

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

# FLKM-I/O - Optocoupler module



2282075

<https://www.phoenixcontact.com/us/products/2282075>

## Mounting

Assembly note	in rows with zero spacing
Mounting position	any

# FLKM-I/O - Optocoupler module



2282075

<https://www.phoenixcontact.com/us/products/2282075>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2282075>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705

# FLKM-I/O - Optocoupler module

2282075

<https://www.phoenixcontact.com/us/products/2282075>



## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

# FLKM-I/O - Optocoupler module



2282075

<https://www.phoenixcontact.com/us/products/2282075>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)