

# AXC 1050 PN STARTERKIT - Starter kit



2400361

<https://www.phoenixcontact.com/us/products/2400361>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

AXC 1050 PN starter kit including AXC 1050 controller, AXL F BK PN bus coupler, AXL F DI/DO 16 I/O modules, power supply, PC Worx software with quick start guide, and additional accessories



## Your advantages

- Quick entry into automation with PROFINET thanks to step-by-step instructions for the test setup
- Structure with the latest automation station based on Axiocontrol and AxioLine components
- Get started right away with a set of all required products

## Commercial data

Item number	2400361
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR10
Product key	DRAAEA
GTIN	4055626023250
Weight per piece (including packing)	1,789 g
Weight per piece (excluding packing)	1,789 g
Customs tariff number	85371091
Country of origin	DE

# AXC 1050 PN STARTERKIT - Starter kit



2400361

<https://www.phoenixcontact.com/us/products/2400361>

## Set consists of

### AXC 1050 - Controller

2700988

<https://www.phoenixcontact.com/us/products/2700988>



Axio control for direct open-loop control of Axioline I/Os. With 2 Ethernet interfaces and programming capabilities according to IEC 61131-3. Complete with connector connector and labeling field.

---

### AXL F BK PN - Bus coupler

2701815

<https://www.phoenixcontact.com/us/products/2701815>



Axioline F, Bus coupler, PROFINET, RJ45 jack, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connector

# AXC 1050 PN STARTERKIT - Starter kit

2400361

<https://www.phoenixcontact.com/us/products/2400361>

## AXL F DI16/4 2F - Digital module

2688022

<https://www.phoenixcontact.com/us/products/2688022>



Axioline F, Digital input module, Digital inputs: 16, 24 V DC, connection technology: 4-conductor, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connectors

---

## AXL F DO16/3 2F - Digital module

2688048

<https://www.phoenixcontact.com/us/products/2688048>



Axioline F, Digital output module, Digital outputs: 16, 24 V DC, 500 mA, connection technology: 3-conductor, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connectors

# AXC 1050 PN STARTERKIT - Starter kit



2400361

<https://www.phoenixcontact.com/us/products/2400361>

## STEP-PS/ 1AC/24DC/1.75 - Power supply

2868648

<https://www.phoenixcontact.com/us/products/2868648>



Primary-switched STEP POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/1.75 A

---

## FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>



Patch cable, CAT5, assembled, 1 m

# AXC 1050 PN STARTERKIT - Starter kit

2400361

<https://www.phoenixcontact.com/us/products/2400361>



## CAB-USB A/MICRO USB B/2,0M - Connecting cable

2701626

<https://www.phoenixcontact.com/us/products/2701626>



Connecting cable, for connecting the controller to a PC for PC Worx and LOGIC+, USB A to micro USB B, 2 m in length.

# AXC 1050 PN STARTERKIT - Starter kit



2400361

<https://www.phoenixcontact.com/us/products/2400361>

## Technical data

### Product properties

Product type	Starter kit
Product family	Axoline

# AXC 1050 PN STARTERKIT - Starter kit



2400361

<https://www.phoenixcontact.com/us/products/2400361>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)