

# ITC 8113 GSK 02 - Tablet PC



2403267

<https://www.phoenixcontact.com/us/products/2403267>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Tablet PC, 33.8 cm / 13.3"-TFT display (projective-capacitive, ten-touch control), 1920 x 1080 pixel(s) (Full HD), Intel® Core™ i5 4300U 1.9 GHz, 2x USB 3.0, 1x USB 3.0 inset, WLAN 802.11 a/g/n, Bluetooth 4.0 Class 1+2, 1 x Ethernet (10/100/1000 Mbps), RJ45, Windows® 7 Professional (64-Bit).



Similar figure

## Commercial data

Item number	2403267
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBBAF
GTIN	4055626271569
Customs tariff number	84713000
Country of origin	DE

## Technical data

### Product properties

Product type	Panel PC
--------------	----------

### Computer data

Processor	Intel® Core™ i5 4300U 1.9 GHz
Operating system	Windows® 7 Professional (64-Bit)
RAM	8 GB DDR3
Data storage system	2.5" SSD, 120 GB (SATA)
Camera	5 megapixels with mechanical autofocus
Optional keys	6 additional keys (on/off button, software keyboard, switch task Alt + ESC, right mouse button, user-specific function, SHIFT key (brightness and volume))

### Display

Display type	33.8 cm / 13.3"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive, ten-touch control
Display lighting type	LED
MTBF	> 50000 h
Graphics card	Intel® HD Graphics

### Electrical properties

#### Supply

Power supply unit	20 V/3.5 A external
-------------------	---------------------

### Energy storage

Number of battery slots	2
Battery technology	Lithium-Ion (Smart battery)

### Interfaces

Interfaces	2x USB 3.0
	1x USB 3.0 inset
	WLAN 802.11 a/g/n
	Bluetooth 4.0 Class 1+2
Network	1 x Ethernet (10/100/1000 Mbps), RJ45

### Dimensions

Width	356 mm
Height	262 mm
Depth	42 mm
Note on dimensions	73 mm with folded-out supporting feet

#### External dimensions

# ITC 8113 GSK 02 - Tablet PC



2403267

<https://www.phoenixcontact.com/us/products/2403267>

Width / Height / Depth	356 mm / 262 mm / 42 mm (73 mm with folded-out supporting feet)
------------------------	---

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP53
Ambient temperature (operation)	0 °C ... 40 °C
Permissible humidity (operation)	10 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 85 % (non-condensing)

## Mounting

Mounting type	Mobile application
---------------	--------------------

# ITC 8113 GSK 02 - Tablet PC

2403267

<https://www.phoenixcontact.com/us/products/2403267>



## Classifications

### UNSPSC

UNSPSC 21.0	43211509
-------------	----------

# ITC 8113 GSK 02 - Tablet PC



2403267

<https://www.phoenixcontact.com/us/products/2403267>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)