

VISU+ 2 RT UNLIMITED AD - Visualization software



2700566

<https://www.phoenixcontact.com/us/products/2700566>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Runtime license for Visu+ including alarm dispatcher function where the I/O data and variables in scripting are not limited.

Your advantages

- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Control coupling with OPC

Commercial data

Item number	2700566
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR13
Product key	DRDAAB
GTIN	4046356582711
Weight per piece (including packing)	41.5 g
Weight per piece (excluding packing)	39.1 g
Customs tariff number	49119900
Country of origin	DE

Technical data

Product properties

Product type	Visualization
--------------	---------------

System properties

Intended use for the software	Visualization
-------------------------------	---------------

License information

Type of license	Runtime license
-----------------	-----------------

Functionality

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Advanced alarm management with SMS, FAX, e-mail and voice mail function
Integrated function	Online configuration
	Password protection
	Language selection
	Alarm management
Number of I/O nodes	128000

System requirements

Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Screen resolution	1024 x 768 pixel(s) (XGA)

System requirements for development environment

Operating equipment	Keyboard, mouse
Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
Windows® Server 2003	

2700566

<https://www.phoenixcontact.com/us/products/2700566>

System requirements for runtime environment

Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® XP Embedded
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003
	Windows® CE 5.0
	Windows® CE 6.0
Windows® Mobile	

2700566

<https://www.phoenixcontact.com/us/products/2700566>

Classifications

ECLASS

ECLASS-13.0

27242502

ETIM

ETIM 9.0

EC001416

UNSPSC

UNSPSC 21.0

43231500

2700566

<https://www.phoenixcontact.com/us/products/2700566>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com