

FL SFP FE WDM20-B - Media module



2702438

<https://www.phoenixcontact.com/us/products/2702438>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fast Ethernet SFP WDM module for transmission up to a maximum of 20 km on a single fiber with a wavelength of 1550/1310 nm.

Product description

SFP WDM module with a data transmission speed of 100 Mbps, a wavelength of 1310/1550 nm, and a maximum transmission length of 20 km.

Your advantages

- MSA compliant

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2702438 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN22 |
| Product key | DNN1ZS |
| GTIN | 4055626189147 |
| Weight per piece (including packing) | 36.3 g |
| Weight per piece (excluding packing) | 33 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SFP FE WDM20-B - Media module



2702438

<https://www.phoenixcontact.com/us/products/2702438>

Technical data

Dimensions

| | |
|--------|---------|
| Width | 13.7 mm |
| Height | 8.95 mm |
| Length | 56.5 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|------------------|-------|
| Housing material | Metal |
|------------------|-------|

Mounting

| | |
|---------------|--------------------|
| Mounting type | Plug-in mounting |
| Mounting type | Insert in SFP slot |

Interfaces

Ethernet FO

| | |
|------------------------------|-------------------------------------|
| Connection method | LC |
| Transmission speed | 100 Mbps |
| Transmit capacity, minimum | -14 dBm |
| Transmit capacity, maximum | -8 dBm |
| Minimum receiver sensitivity | -32 dBm |
| Maximum receiver sensitivity | -3 dBm |
| Transmission physics | Single-mode fiberglass |
| Transmission length | 20 km (Fiberglass 9/125) |
| Wavelength | 1550 nm (TX) 1310 nm (RX) |
| Signal LEDs | depending on the Factoryline device |
| No. of channels | 1 (LC single mode) |

Product properties

| | |
|--------------|--|
| Product type | SFP module |
| Type | Factoryline devices with SFP slot |
| MTTF | 221 Years (Telcordia SR-332, temperature factor at 40°C = 1, stress factor at 50% = 1, environmental factor = 1) |
| Format | SFP (Small Form-factor Pluggable) |

Signaling

| | |
|----------------|--------------------------|
| Status display | via a Factoryline device |
|----------------|--------------------------|

2702438

<https://www.phoenixcontact.com/us/products/2702438>

Electrical properties

| | |
|---|--------|
| Current consumption | 300 mA |
| Maximum power dissipation for nominal condition | 1 W |
| Transmission medium | FO |

Supply

| | |
|--------------------------|--------------------------------|
| Supply voltage | 3.3 V (via Factoryline switch) |
| Power supply connection | via SFP slot |
| Max. current consumption | 300 mA |
| Current consumption | 300 mA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-----------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 75 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C (non-condensing) |
| Case temperature | max. 85 °C (Operation) |

Standards and regulations

| | |
|--------------------------|------------------------|
| Standard designation | Laser equipment safety |
| Standards/specifications | IEC 60825 |

FL SFP FE WDM20-B - Media module



2702438

<https://www.phoenixcontact.com/us/products/2702438>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702438>



DNV GL

Approval ID: TAA00000YV



LR

Approval ID: LR22250919TA



NK

Approval ID: TA24215M



BV

Approval ID: 48146_B1 BV

BSH

Approval ID: Nr. 966



RINA

Approval ID: ELE014724XG001

ABS

Approval ID: 21_2066186_1_PDA

FL SFP FE WDM20-B - Media module



2702438

<https://www.phoenixcontact.com/us/products/2702438>

Classifications

ECLASS

ECLASS-13.0

19179090

ETIM

ETIM 9.0

EC000310

UNSPSC

UNSPSC 21.0

43222600

FL SFP FE WDM20-B - Media module



2702438

<https://www.phoenixcontact.com/us/products/2702438>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com