

# UM108-SEFE/R-A73 BK - Lateral element



2707615

<https://www.phoenixcontact.com/us/products/2707615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Lateral element with foot, 5 mm wide (right), for assembly on NS 32 or NS 35/7.5, tall design, for 73 mm-wide U-profile cover

## Commercial data

Item number	2707615
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918903145
Weight per piece (including packing)	18.59 g
Weight per piece (excluding packing)	18.33 g
Customs tariff number	39269097
Country of origin	PL

# UM108-SEFE/R-A73 BK - Lateral element



2707615

<https://www.phoenixcontact.com/us/products/2707615>

## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

### Material specifications

Color (Side element)	black (RAL 9005)
Material Lateral element	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

# UM108-SEFE/R-A73 BK - Lateral element



2707615

<https://www.phoenixcontact.com/us/products/2707615>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2707615>



**UL Recognized**

Approval ID: E240868

# UM108-SEFE/R-A73 BK - Lateral element



2707615

<https://www.phoenixcontact.com/us/products/2707615>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM108-SEFE/R-A73 BK - Lateral element



2707615

<https://www.phoenixcontact.com/us/products/2707615>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.114 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)