

UM108-SEFE/L-A73 BK - Lateral element



2707628

<https://www.phoenixcontact.com/us/products/2707628>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Lateral element with foot, 5 mm wide (left), for assembly on NS 32 or NS 35/7.5, tall design, for 73 mm-wide U-profile cover

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2707628 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC13 |
| Product key | ACHDBA |
| GTIN | 4017918903152 |
| Weight per piece (including packing) | 18.3 g |
| Weight per piece (excluding packing) | 16.8 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

2707628

<https://www.phoenixcontact.com/us/products/2707628>

Technical data

Product properties

| | |
|------------------------------|-------------------------------|
| Product type | Panel mounting base side part |
| Housing type | Press-drawn section housings |
| Housing series | UM |
| Product family | UM108 |
| Ventilation openings present | no |

Dimensions

| | |
|-------|--------|
| Depth | 125 mm |
|-------|--------|

Material specifications

| | |
|--|------------------|
| Color (Side element) | black (RAL 9005) |
| Material Lateral element | PA |
| Flammability rating according to UL 94 | V0 |
| Surface characteristics | untreated |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
|---------------------------------|--|

PCB data

| | |
|-----------------------|---|
| Number of PCB holders | 2 |
|-----------------------|---|

Mounting

| | |
|---------------|---|
| Mounting type | DIN rail mounting, screw connection with extruded profile |
|---------------|---|

UM108-SEFE/L-A73 BK - Lateral element



2707628

<https://www.phoenixcontact.com/us/products/2707628>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2707628>



UL Recognized

Approval ID: E240868

UM108-SEFE/L-A73 BK - Lateral element



2707628

<https://www.phoenixcontact.com/us/products/2707628>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM108-SEFE/L-A73 BK - Lateral element



2707628

<https://www.phoenixcontact.com/us/products/2707628>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com