

MPB 18/1- 7/1.0.0 - Wiring bridge

2817877

<https://www.phoenixcontact.com/us/products/2817877>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wiring bridge with forked contact tabs for biconnect terminal blocks.
Contact tabs with 17.5 mm pitch in arranged in irregular pitch steps.
For wiring applications with lightning current and surge voltage arresters.

Commercial data

Item number	2817877
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CL18
Product key	CL132Z
GTIN	4017918148218
Weight per piece (including packing)	25.52 g
Weight per piece (excluding packing)	22.84 g
Customs tariff number	85369095
Country of origin	DE

MPB 18/1- 7/1.0.0 - Wiring bridge



2817877

<https://www.phoenixcontact.com/us/products/2817877>

Technical data

Product properties

Product type	Bridge
Type	Comb bridge
Number of positions	7

Electrical properties

Number of phases	1
Nominal current I_N	100 A

Material specifications

Housing material	Plastic
------------------	---------

MPB 18/1- 7/1.0.0 - Wiring bridge



2817877

<https://www.phoenixcontact.com/us/products/2817877>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com