

# IBS OPTOSUB-F/L-LK-OPC-2MBD - Fiber optic adapter

2878023

<https://www.phoenixcontact.com/us/products/2878023>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



INTERBUS fiber optic adapter, for converting the remote IN interface to fiber optics, FO output left, correction of the optical transmission power, 2 MBD

## Commercial data

Item number	2878023
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR14
Product key	DREDDA
GTIN	4046356048422
Weight per piece (including packing)	62.8 g
Weight per piece (excluding packing)	49.64 g
Customs tariff number	85176200
Country of origin	DE

# IBS OPTOSUB-F/L-LK-OPC-2MBD - Fiber optic adapter



2878023

<https://www.phoenixcontact.com/us/products/2878023>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Media converter
--------------	-----------------

### Interfaces

Signal	INTERBUS
--------	----------

#### Data: optical FO

Connection method	F-SMA
Wavelength	660 nm
Transmission medium	FO

#### Data: Incoming remote bus

Bus system	INTERBUS
Transmission speed	2 Mbps
Connection method	D-SUB 9 plug
Transmission length	35 m (50 m system without optical path diagnostics) 50 m (70 m system with optical path diagnostics)

### Dimensions

Width	65 mm
Height	16 mm
Depth	59 mm

### Material specifications

Color	green
-------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C

# IBS OPTOSUB-F/L-LK-OPC-2MBD - Fiber optic adapter



2878023

<https://www.phoenixcontact.com/us/products/2878023>

## Classifications

### ECLASS

ECLASS-13.0

27242208

### ETIM

ETIM 9.0

EC001423

### UNSPSC

UNSPSC 21.0

32151700

# IBS OPTOSUB-F/L-LK-OPC-2MBD - Fiber optic adapter



2878023

<https://www.phoenixcontact.com/us/products/2878023>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	655a6e7e-8b1b-4624-bea6-7299ccb2c5e4

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)