

RIF-3-BPT/3X21 - Relay base



2900938

<https://www.phoenixcontact.com/us/products/2900938>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Relay base RIF-3..., for octal relays with 3 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Commercial data

Item number	2900938
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C465
Product key	DK6524
GTIN	4046356733052
Weight per piece (including packing)	78.1 g
Weight per piece (excluding packing)	70 g
Customs tariff number	85366990
Country of origin	CN

RIF-3-BPT/3X21 - Relay base



2900938

<https://www.phoenixcontact.com/us/products/2900938>

Technical data

Product properties

Product type	Relay socket
Product family	RIFLINE complete
Set comprises	2903292 RIF-3-RPT-LV-230AC/3X21
	2903293 RIF-3-RPT-LV-120AC/3X21
	2903294 RIF-3-RPT-LDP-24DC/3X21

Electrical properties

Nominal voltage U_N	250 V AC/DC
Nominal current I_N	max. 12 A (Depends on application/assembly)
Protective circuit	depending on the selected input/suppressor modules

Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
	0.14 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve)
	0.14 mm ² ... 1 mm ² (Ferrule with plastic sleeve, two conductors on double terminal block)
Conductor cross-section AWG	26 ... 16 (solid)
	26 ... 16 (flexible)

Dimensions

Drill hole

Diameter	3.2 mm
Width	40 mm
Height	103 mm
Depth Retaining bracket	90 mm (with retaining bracket)

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94 (Housing)	V2 (Housing)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (Depends on application/assembly)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

Corrosive gas test

RIF-3-BPT/3X21 - Relay base



2900938

<https://www.phoenixcontact.com/us/products/2900938>

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

Mounting

Mounting type	DIN rail mounting
Mounting position	any

RIF-3-BPT/3X21 - Relay base



2900938


<https://www.phoenixcontact.com/us/products/2900938>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900938>

 **CSA**
Approval ID: 76787

 **UL Recognized**
Approval ID: FILE E 113228

 **EAC**
Approval ID: RU D-DE.B*00573/18

DNV
Approval ID: TAA000018V

RIF-3-BPT/3X21 - Relay base



2900938

<https://www.phoenixcontact.com/us/products/2900938>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 10.0	EC001456
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

RIF-3-BPT/3X21 - Relay base



2900938

<https://www.phoenixcontact.com/us/products/2900938>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com