

POSI 125DC/48DC/15 - Solid-state relay



2912141

<https://www.phoenixcontact.com/us/products/2912141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	2912141
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61BY
GTIN	4017918240530
Weight per piece (including packing)	56.85 g
Weight per piece (excluding packing)	56.85 g
Customs tariff number	85364900
Country of origin	DE

POSI 125DC/48DC/15 - Solid-state relay



2912141

<https://www.phoenixcontact.com/us/products/2912141>

Technical data

Product properties

Product type	Solid-state relay module
--------------	--------------------------

Data management status

Date of last data management	15.09.2025
------------------------------	------------

POSI 125DC/48DC/15 - Solid-state relay



2912141

<https://www.phoenixcontact.com/us/products/2912141>

Classifications

ECLASS

ECLASS-13.0	27371604
ECLASS-15.0	27371604

ETIM

ETIM 10.0	EC001504
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

POSI 125DC/48DC/15 - Solid-state relay



2912141

<https://www.phoenixcontact.com/us/products/2912141>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com