

Software - VISU+ 2 RT 1024 - 2988641

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Runtime license for Visu+ where the I/O data and variables in scripting are limited to 1024 bytes.

Your advantages

- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Control coupling with OPC
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Access protection with user management



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 479714 |
| GTIN | 4046356479714 |

Technical data

License information

| | |
|-------------------------------|-----------------|
| Intended use for the software | Visualization |
| Type of license | Runtime license |

Functions

| | |
|---------------------|--|
| Basic functions | Know-How protection and safety through encoding of projects |
| | Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server |
| | FDA CFR 21 Part 11 compatible |
| Integrated function | Online configuration |
| | Password protection |

Software - VISU+ 2 RT 1024 - 2988641

Technical data

Functions

| | |
|---------------------|--------------------|
| | Language selection |
| Number of I/O nodes | 1024 I/O bytes |

Hardware requirements

| | |
|-------------------|---|
| Hard disk | min. 1 GByte (recommended: 2 GB) |
| RAM | min. 1 GByte (2 GB for Windows Vista and Windows 7) |
| CPU | Pentium/Celeron, 1.6 GHz |
| Optical drive | DVD-ROM |
| Screen resolution | rec. 1024 pixel(s) x 768 pixel(s) (XGA) |

Software requirements

| | |
|---------------------|----------------------------------|
| Languages supported | German, English, French, Italian |
| Supported browsers | Internet Explorer 5.5 or higher |

Development environment requirements

| | |
|---------------------------------|--|
| Operating equipment | Keyboard, mouse |
| Operating system | Windows® 10 |
| | Windows® 8.1 |
| | Windows® 8 |
| | Windows® 7 |
| | Windows® Embedded Standard 7 |
| | Windows® Server 2019 |
| | Windows® Server 2016 |
| | Windows® Server 2012 R2 |
| | Windows® Server 2012 |
| | Windows® Server 2008 R2 |
| | Windows® Server 2008 |
| | Windows® Server 2003 |
| Note about the operating system | Server Core installations are not supported. |

Runtime environment requirements

| | |
|------------------|------------------------------|
| Operating system | Windows® 10 |
| | Windows® 8.1 |
| | Windows® 8 |
| | Windows® 7 |
| | Windows® Embedded Standard 7 |
| | Windows® XP Embedded |
| | Windows® Server 2019 |
| | Windows® Server 2016 |
| | Windows® Server 2012 R2 |

Software - VISU+ 2 RT 1024 - 2988641

Technical data

Runtime environment requirements

| | |
|--|-------------------------|
| | Windows® Server 2012 |
| | Windows® Server 2008 R2 |
| | Windows® Server 2008 |
| | Windows® Server 2003 |
| | Windows® CE 5.0 |
| | Windows® CE 6.0 |
| | Windows® Mobile |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27242502 |
| eCl@ss 11.0 | 27242502 |
| eCl@ss 4.0 | 27338000 |
| eCl@ss 4.1 | 27338000 |
| eCl@ss 5.0 | 27242500 |
| eCl@ss 5.1 | 27242500 |
| eCl@ss 6.0 | 27242500 |
| eCl@ss 7.0 | 27242502 |
| eCl@ss 9.0 | 27242502 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001416 |
| ETIM 3.0 | EC001416 |
| ETIM 4.0 | EC001416 |
| ETIM 6.0 | EC001416 |
| ETIM 7.0 | EC001416 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43163005 |
| UNSPSC 7.0901 | 43232404 |
| UNSPSC 11 | 43163005 |
| UNSPSC 12.01 | 43232404 |
| UNSPSC 13.2 | 43231507 |
| UNSPSC 18.0 | 43231507 |
| UNSPSC 19.0 | 43231507 |
| UNSPSC 20.0 | 43231507 |
| UNSPSC 21.0 | 43231507 |

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>