

# FBSTB 80-ZDIK GY - Plug-in bridge



3006564

<https://www.phoenixcontact.com/us/products/3006564>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in bridge, pitch: 5.2 mm, number of positions: 80, nominal current: 32 A, color: gray

## Commercial data

Item number	3006564
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE29
Product key	BE2Z2X
GTIN	4017918147051
Weight per piece (including packing)	35.84 g
Weight per piece (excluding packing)	32.045 g
Customs tariff number	85366990
Country of origin	PL

# FBSTB 80-ZDIK GY - Plug-in bridge



3006564

<https://www.phoenixcontact.com/us/products/3006564>

## Technical data

### Product properties

Product type	Plug-in bridge
Number of positions	80
Pitch	5.2 mm

### Electrical properties

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

### Connection data

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

### Dimensions

Pitch	5.2 mm
-------	--------

### Material specifications

Color	gray
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# FBSTB 80-ZDIK GY - Plug-in bridge



3006564

<https://www.phoenixcontact.com/us/products/3006564>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)