


UKK 5-R 3,3K/O-U - Component terminal block



3026984

<https://www.phoenixcontact.com/us/products/3026984>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component terminal block, with 3.3 kOhm resistor, from top to bottom, nominal current: 32 A, connection method: Screw connection, 1 level, Rated cross section: 4 mm², cross section: 0.2 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

Commercial data

Item number	3026984
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE12
Product key	BE1273
GTIN	4046356158381
Weight per piece (including packing)	15.94 g
Weight per piece (excluding packing)	15.94 g
Customs tariff number	85369010
Country of origin	PL

UKK 5-R 3,3K/O-U - Component terminal block



3026984

<https://www.phoenixcontact.com/us/products/3026984>

Technical data

Product properties

Product type	Component terminal block
Number of connections	3
Number of rows	2
Potentials	2

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
---------------------	------

Connection data

Number of connections per level	2
Nominal cross section	4 mm ²

1 level

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	8 mm
Internal cylindrical gage	A4
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section, flexible [AWG]	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, rigid	4 mm ²
Cross-section with insertion bridge, flexible	2.5 mm ²
2 conductors with same cross section, rigid	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Nominal cross section	4 mm ²
Nominal current	32 A
Maximum load current	32 A (with 4 mm ² conductor cross-section)

Dimensions

Width	6.2 mm
-------	--------

UKK 5-R 3,3K/O-U - Component terminal block



3026984

<https://www.phoenixcontact.com/us/products/3026984>

End cover width	2.5 mm
-----------------	--------

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

UKK 5-R 3,3K/O-U - Component terminal block




3026984

<https://www.phoenixcontact.com/us/products/3026984>

Drawings

Circuit diagram



Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com