

APH-RSCWE 6-3 CARRIER - Cover profile carrier



3069058

<https://www.phoenixcontact.com/us/products/3069058>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover profile carrier, for accommodating the cover profile, depth: 73.1 mm, width: 8.15 mm, height: 81 mm, number of positions: 1, color: gray, mounting type: Snap in

Commercial data

Item number	3069058
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626157566
Weight per piece (including packing)	12.37 g
Weight per piece (excluding packing)	12.2 g
Customs tariff number	39269097
Country of origin	PL

3069058

<https://www.phoenixcontact.com/us/products/3069058>

Technical data

Product properties

Product type	Cover profile carrier
Number of positions	1

Insulation characteristics

Overvoltage category	III
----------------------	-----

Dimensions

Width	8.15 mm
Height	81 mm
Depth	73.1 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0
Insulating material group	I
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Snap in
---------------	---------

APH-RSCWE 6-3 CARRIER - Cover profile carrier



3069058

<https://www.phoenixcontact.com/us/products/3069058>

Classifications

ECLASS

ECLASS-15.0	27250302
ECLASS-13.0	27182807

ETIM

ETIM 10.0	EC001041
-----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

APH-RSCWE 6-3 CARRIER - Cover profile carrier



3069058

<https://www.phoenixcontact.com/us/products/3069058>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.109 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com