

# SKS 14-D - Shield connection terminal block



3240214

<https://www.phoenixcontact.com/us/products/3240214>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Shield connection terminal block, for direct shield on conductive mounting panels



## Your advantages

- As components, it is not possible to certify shield connections in accordance with the requirements of the directive and standards for electrical equipment in potentially explosive areas. As such, shield connection clamps can be used in the Ex area even without an appropriate approval or marking.
- Three different mounting types supported: on NS 35 DIN rails, on busbars, or directly on conductive mounting panels

## Commercial data

Item number	3240214
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE75
Product key	BE7521
GTIN	4046356458894
Weight per piece (including packing)	20.35 g
Weight per piece (excluding packing)	19.96 g
Customs tariff number	85369010
Country of origin	DE

# SKS 14-D - Shield connection terminal block



3240214

<https://www.phoenixcontact.com/us/products/3240214>

## Technical data

### Product properties

Product type	Shield connection clamp
Pitch	19 mm
Number of connections	1
Number of rows	1

### Electrical properties

Maximum power dissipation for nominal condition	1.02 W
---	--------

### Connection data

Grounding foot	Yes
Connection method	Spring-cage connection
Screw thread	M4
Conductor cross-section rigid	4 mm <sup>2</sup> ... 13.5 mm <sup>2</sup>
Cross section AWG	10 ... 8 (converted acc. to IEC)
Conductor cross-section flexible	4 mm <sup>2</sup> ... 13.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	10 ... 8 (converted acc. to IEC)

### Dimensions

Width	19 mm
Height	21 mm
Depth	40.7 mm
Pitch	19 mm

### Material specifications

Color	silver-colored
Material	Steel

### Cable/line

External cable diameter	3 mm ... 14 mm
-------------------------	----------------

### Mechanical properties

#### Mechanical data

Open side panel	No
-----------------	----

### Mounting

Mounting type	direct screw connection
---------------	-------------------------

# SKS 14-D - Shield connection terminal block



3240214

<https://www.phoenixcontact.com/us/products/3240214>

## Classifications

### ECLASS

ECLASS-13.0	27250309
ECLASS-15.0	27250309

### ETIM

ETIM 10.0	EC002020
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SKS 14-D - Shield connection terminal block



3240214

<https://www.phoenixcontact.com/us/products/3240214>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.223 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)