

# WP-GR HF IP69K PG11 BK - Protective hose screw connection



3240932

<https://www.phoenixcontact.com/us/products/3240932>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, Pg thread, IP68/69k protection, with strain relief

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240932       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 20 pc         |
| Sales key                            | BF68          |
| Product key                          | AF7DSA        |
| GTIN                                 | 4046356710398 |
| Weight per piece (including packing) | 13.88 g       |
| Weight per piece (excluding packing) | 13.88 g       |
| Customs tariff number                | 39174000      |
| Country of origin                    | DE            |

# WP-GR HF IP69K PG11 BK - Protective hose screw connection



3240932

<https://www.phoenixcontact.com/us/products/3240932>

## Technical data

### Product properties

|                              |                                  |
|------------------------------|----------------------------------|
| Product type                 | Protective hose screw connection |
| Application                  | Cable gland                      |
| Type of the screw connection | Conduit adapter                  |
| Cable outlet                 | straight                         |
| Thread type                  | Pg                               |

### Dimensions

|                          |                |
|--------------------------|----------------|
| Width                    | 23 mm          |
| Height                   | 59 mm          |
| Wrench size              | 21 mm          |
| Wrench size for mounting | 21 mm<br>22 mm |

### Material specifications

|  |  |
|--|--|
| Material                               | PA 6                                     |
| Flammability rating according to UL 94 | V2                                       |
| Material for screw connection          | PA                                       |
| Components                             | free from silicone, halogen, and cadmium |

### Cable/line

|              |     |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

### Mechanical properties

#### Mechanical data

|                              |                 |
|------------------------------|-----------------|
| Type of the screw connection | Conduit adapter |
|------------------------------|-----------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Degree of protection            | IP68<br>IP69K     |
| Ambient temperature (operation) | -40 °C ... 120 °C |

# WP-GR HF IP69K PG11 BK - Protective hose screw connection



3240932

<https://www.phoenixcontact.com/us/products/3240932>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27430311 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001178 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

# WP-GR HF IP69K PG11 BK - Protective hose screw connection



3240932

<https://www.phoenixcontact.com/us/products/3240932>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)