

# WP-SC PA HF 28,5 BK - Cable protection end sleeve



3240985

<https://www.phoenixcontact.com/us/products/3240985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable protection end sleeve, material: PA 6, color: black, flammability rating in acc. with UL 94: V2, inside diameter: 20.8 mm

## Commercial data

Item number	3240985
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356711036
Weight per piece (including packing)	4.256 g
Weight per piece (excluding packing)	3.294 g
Customs tariff number	39174000
Country of origin	DE

# WP-SC PA HF 28,5 BK - Cable protection end sleeve



3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Technical data

### Product properties

Product type	Protective cap
--------------	----------------

### Dimensions

Length	22 mm
Diameter	28.5 mm

### Internal dimensions

Internal diameter	20.8 mm
-------------------	---------

### Material specifications

Material	PA 6
Flammability rating according to UL 94	V2
Components	halogen-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

# WP-SC PA HF 28,5 BK - Cable protection end sleeve



3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240985>



**UL Recognized**  
Approval ID: E86359



LR

3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Classifications

### ECLASS

ECLASS-15.0	27430316
ECLASS-13.0	27430316

### ETIM

ETIM 10.0	EC000519
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.386 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)