

WP-GT BRASS M10 - Protective hose screw connection



3241030

<https://www.phoenixcontact.com/us/products/3241030>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable gland made from brass with metric thread, rotatable, IP40 protection



Commercial data

Item number	3241030
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356711661
Weight per piece (including packing)	15.73 g
Weight per piece (excluding packing)	15.73 g
Customs tariff number	74122000
Country of origin	DE

WP-GT BRASS M10 - Protective hose screw connection



3241030

<https://www.phoenixcontact.com/us/products/3241030>

Technical data

Product properties

Product type	Protective hose screw connection
Cable outlet	straight
Thread type	metric

Dimensions

Width	17 mm
Height	32 mm
Length	32 mm
Wrench size	15 mm
Wrench size for mounting	15 mm

External dimensions

Outside diameter	10 mm
------------------	-------

Internal dimensions

Internal diameter	6 mm
-------------------	------

Material specifications

Color	brass color
Material	Brass, nickel-plated
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-40 °C ... 250 °C

WP-GT BRASS M10 - Protective hose screw connection



3241030

<https://www.phoenixcontact.com/us/products/3241030>

Classifications

ECLASS

ECLASS-13.0

27430310

ETIM

ETIM 9.0

EC001180

UNSPSC

UNSPSC 21.0

40141700

WP-GT BRASS M10 - Protective hose screw connection



3241030

<https://www.phoenixcontact.com/us/products/3241030>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d3154ac1-98d7-4305-b706-8a8a440204ef

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com