

# WP-CN PA M40 - Counter nut



3241137

<https://www.phoenixcontact.com/us/products/3241137>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M40, color: gray



## Your advantages

- The polyamide counter nuts are used to lock protective hose screw connections in the case of bore holes without a thread.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3241137       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BF68          |
| Product key                          | AF7DSA        |
| GTIN                                 | 4046356785433 |
| Weight per piece (including packing) | 6.532 g       |
| Weight per piece (excluding packing) | 3.272 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# WP-CN PA M40 - Counter nut



3241137

<https://www.phoenixcontact.com/us/products/3241137>

## Technical data

### Product properties

|              |          |
|--------------|----------|
| Product type | Flat nut |
| Thread type  | M40      |

### Dimensions

|                             |      |
|-----------------------------|------|
| Height                      | 7 mm |
| Thread type connection side | M40  |

### Material specifications

|          |                                 |
|----------|---------------------------------|
| Material | Polyamide fiberglass reinforced |
|----------|---------------------------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

# WP-CN PA M40 - Counter nut



3241137

<https://www.phoenixcontact.com/us/products/3241137>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140807 |
| ECLASS-15.0 | 27140807 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003608 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31161700 |
|-------------|----------|

# WP-CN PA M40 - Counter nut



3241137

<https://www.phoenixcontact.com/us/products/3241137>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.328 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)