

# WP-OR M16 - Sealing ring

3241189

<https://www.phoenixcontact.com/us/products/3241189>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing ring, for threads M16, color: black



## Your advantages

- The properties of the Perbunan O-rings, such as their resistance to oil and seal against water and dust, mean that they can be used in a wide range of applications

## Commercial data

Item number	3241189
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356785952
Weight per piece (including packing)	0.238 g
Weight per piece (excluding packing)	0.238 g
Customs tariff number	40169300
Country of origin	DE

# WP-OR M16 - Sealing ring

3241189

<https://www.phoenixcontact.com/us/products/3241189>



## Technical data

### Product properties

Product type	Seal
Thread type	M16

### Dimensions

Height	2 mm
Thread type connection side	M16

### Internal dimensions

Internal diameter	14 mm
-------------------	-------

### Material specifications

Material	Perbunan
----------	----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 120 °C
---------------------------------	-------------------

# WP-OR M16 - Sealing ring

3241189

<https://www.phoenixcontact.com/us/products/3241189>



## Classifications

### ECLASS

ECLASS-13.0	27430319
ECLASS-15.0	27430319

### ETIM

ETIM 10.0	EC001181
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# WP-OR M16 - Sealing ring



3241189

<https://www.phoenixcontact.com/us/products/3241189>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)