

# WP-GR HF CTA M20 BK - Protective hose screw connection



3241220

<https://www.phoenixcontact.com/us/products/3241220>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Corrugated pipe adapter, with internal thread, for connecting corrugated pipes to HEAVYCON EVO M20 plastic cable glands or ADVANCE M20 plastic housings, straight, black, IP66.

## Commercial data

Item number	3241220
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356860826
Weight per piece (including packing)	14.71 g
Weight per piece (excluding packing)	14.71 g
Customs tariff number	39269097
Country of origin	DE

# WP-GR HF CTA M20 BK - Protective hose screw connection



3241220

<https://www.phoenixcontact.com/us/products/3241220>

## Technical data

### Product properties

Product type	Protective hose screw connection
Application	Cable gland
Thread type	metric

### Material specifications

Material	PA
Flammability rating according to UL 94	V2
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 115 °C

### Mounting

Assembly note	The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used.
---------------	--

# WP-GR HF CTA M20 BK - Protective hose screw connection



3241220

<https://www.phoenixcontact.com/us/products/3241220>

## Classifications

### ECLASS

ECLASS-13.0	27430311
ECLASS-15.0	27430311

### ETIM

ETIM 10.0	EC001178
-----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# WP-GR HF CTA M20 BK - Protective hose screw connection



3241220

<https://www.phoenixcontact.com/us/products/3241220>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.476 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)