

# D-BT 1,25 - End cover

3281120

<https://www.phoenixcontact.com/us/products/3281120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, width: 3.5 mm, height: 26 mm, color: black



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 3281120                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BE59                           |
| Product key                          | BE5Z1X                         |
| GTIN                                 | 4055626119182                  |
| Weight per piece (including packing) | 2.05 g                         |
| Weight per piece (excluding packing) | 2.046 g                        |
| Customs tariff number                | 85389099                       |
| Country of origin                    | IN                             |

# D-BT 1,25 - End cover



3281120

<https://www.phoenixcontact.com/us/products/3281120>

## Technical data

### Product properties

|              |           |
|--------------|-----------|
| Product type | End cover |
|--------------|-----------|

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
|----------------------|-----|

### Environmental and real-life conditions

#### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C ... 85 °C  |
| Ambient temperature (storage/transport)  | -25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

### Material specifications

|  |       |
|--|-------|
| Color                                  | black |
| Material                               | PC    |
| Flammability rating according to UL 94 | V0    |
| Insulating material group              | IIIa  |

### Dimensions

|                 |        |
|-----------------|--------|
| Width           | 3.5 mm |
| End cover width | 3.5 mm |
| Height          | 26 mm  |

# D-BT 1,25 - End cover

3281120

<https://www.phoenixcontact.com/us/products/3281120>



## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# D-BT 1,25 - End cover



3281120

<https://www.phoenixcontact.com/us/products/3281120>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)