

THERMOMARK ROLL-CUTTER - Cutter



5146422

<https://www.phoenixcontact.com/us/products/5146422>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutter for THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 110 mm, suitable for: TML, SK, EML-RM, PMM, WMS continuous media, WMS-2 HF continuous media, WMS-OT HF, TMT continuous media, and EMT (EX15)R

Your advantages

- Custom length cuts of continuous markers

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 5146422 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG03 |
| Product key | BG122Z |
| GTIN | 4046356528559 |
| Weight per piece (including packing) | 605 g |
| Weight per piece (excluding packing) | 579.9 g |
| Customs tariff number | 82089000 |
| Country of origin | DE |

THERMOMARK ROLL-CUTTER - Cutter



5146422

<https://www.phoenixcontact.com/us/products/5146422>

Technical data

Product properties

Marking

Identification technology

Thermotransfer

THERMOMARK ROLL-CUTTER - Cutter



5146422

<https://www.phoenixcontact.com/us/products/5146422>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5146422>



EAC

Approval ID: KZ 27978

THERMOMARK ROLL-CUTTER - Cutter



5146422

<https://www.phoenixcontact.com/us/products/5146422>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19140620 |
| ECLASS-15.0 | 19140620 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001675 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43211600 |
|-------------|----------|

THERMOMARK ROLL-CUTTER - Cutter



5146422

<https://www.phoenixcontact.com/us/products/5146422>

Environmental product compliance

EU RoHS

| | |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com