

UMK45-REL/KUEP-ST-125DC/1-EHC - Active module



5602114

<https://www.phoenixcontact.com/us/products/5602114>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE relay base for KUEP-style relay



Your advantages

- Safe isolation between coil and contact side

Commercial data

Item number	5602114
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6164
GTIN	4046356688550
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	US

5602114

<https://www.phoenixcontact.com/us/products/5602114>

Technical data

Product properties

Product type	Relay Module
Application	Universal
Operating mode	100% operating factor
Mechanical service life	1x 10 ⁵ cycles

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Test voltage (Winding/contact)	2.2 kV (50 Hz, 1 min., winding/contact)
--------------------------------	---

Input data

Coil side

Nominal input voltage U_N	125 V DC
Typical input current at U_N	14 mA
Typical response time	15 ms
Typical release time	10 ms
Protective circuit	Freewheeling diode
Operating voltage display	LED

Output data

Switching

Contact switching type	1 N/O contact
Contact material	Silver cadmium oxide (AgCdO)
Maximum switching voltage	150 V DC
Limiting continuous current	10 A

Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	30 ... 10

Contact side

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²

UMK45-REL/KUEP-ST-125DC/1-EHC - Active module



5602114

<https://www.phoenixcontact.com/us/products/5602114>

Conductor cross-section AWG	30 ... 10
-----------------------------	-----------

Dimensions

Width	45 mm
Height	77 mm
Depth	85.5 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Mounting

Assembly note	in rows with zero spacing
Mounting position	any

5602114

<https://www.phoenixcontact.com/us/products/5602114>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com