

## Tool set - CRIMPSET 6 - 1202072

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assortment box, metal, supplied with ferrules acc. to DIN 46228-4: 1990-09, 500 pcs. each of AI 0,25-6 YE, AI 0,34-6 TQ, AI 0,5-8 WH, AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK, 300 pcs. AI 2,5-8 BU, 200 pcs. 4-10 GY, 100 pcs. AI 6-12 YE, CRIMPFOX 6T, QUICK WIREFOX 6


### Product Description

Tool set, equipped

### Your advantages

We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 017699
GTIN	4017918017699

### Technical data

#### Dimensions

Length (b)	206 mm
Width (a)	357 mm
Height (c)	48 mm

#### General

Base element material	Metal
-----------------------	-------

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Articles in set

Ferrule - AI 0,25- 6 YE - 3203024



Ferrule, sleeve length: 6 mm, length: 10.5 mm, color: yellow

## Tool set - CRIMPSET 6 - 1202072

### Articles in set

---

Ferrule - AI 0,34- 6 TQ - 3203053



Ferrule, sleeve length: 6 mm, length: 10.5 mm, color: turquoise

---

Ferrule - AI 0,5 - 8 WH - 3200014



Ferrule, sleeve length: 8 mm, length: 14 mm, color: white

---

Ferrule - AI 0,75- 8 GY - 3200519



Ferrule, sleeve length: 8 mm, length: 14 mm, color: gray

---

Ferrule - AI 1 - 8 RD - 3200030



Ferrule, sleeve length: 8 mm, length: 14 mm, color: red

---

Ferrule - AI 1,5 - 8 BK - 3200043



Ferrule, sleeve length: 8 mm, length: 14 mm, color: black

---

## Tool set - CRIMPSET 6 - 1202072

### Articles in set

Ferrule - AI 2,5 - 8 BU - 3200522



Ferrule, sleeve length: 8 mm, length: 14 mm, color: blue

Ferrule - AI 4 -10 GY - 3200535



Ferrule, sleeve length: 10 mm, length: 17 mm, color: gray

Ferrule - AI 6 -12 YE - 3200548



Ferrule, sleeve length: 12 mm, length: 20 mm, color: yellow

Stripping pliers - QUICK WIREFOX 6 - 1204384



Stripping tool for cables with PVC insulation, stripping range: 0.08 to 6 mm<sup>2</sup>, wire cutting up to 6 mm<sup>2</sup> flexible or 4 mm<sup>2</sup> rigid

Crimping pliers - CRIMPFOX DUO 10 - 1031721



Crimping pliers, type of contact: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 0.14 mm<sup>2</sup>, max. cross section: 10 mm<sup>2</sup>, for TWIN ferrules up to 2 x 4 mm<sup>2</sup>, automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, black/green

### Classifications

eCl@ss

eCl@ss 10.0.1	27400218
eCl@ss 4.0	21040300

# Tool set - CRIMPSET 6 - 1202072

## Classifications

### eCl@ss

eCl@ss 4.1	21040300
eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400218
eCl@ss 8.0	27400218
eCl@ss 9.0	27400218

### ETIM

ETIM 2.0	EC000149
ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000524
ETIM 6.0	EC000524
ETIM 7.0	EC000524

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

## Approvals

### Approvals

---

Approvals

EAC / UL Listed / cUL Listed / cULus Listed

---


Ex Approvals

---


### Approval details

## Tool set - CRIMPSET 6 - 1202072

### Approvals

EAC		EAC-Zulassung
-----	---	---------------

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E488001
-----------	---	---	---------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	E488001
------------	---	---	---------

cULus Listed			
--------------	---	--	--

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>