

# Voltage tester - DUSPOL EXPERT - 1209091

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

## Your advantages

- Audible and optical continuity test
- Overvoltage category CAT IV 600 V and CAT III 1000 V according to IEC/EN 61243-3
- Vibration alarm for safe voltage detection
- Shock-proof, dust-proof, and splash-proof housing, IP65
- DC and AC voltage tests in the range from 12 V to 690 V AC/750 V DC, fully functional even without batteries
- Polarity test (+/-) for DC voltage
- Single-pos. test of the phase conductor
- Indicator for the direction of rotating field of a three-phase network as long as the star point is grounded
- Measuring point lighting
- Load connection via pushbutton

RoHS

## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 309905
GTIN	4046356309905

## Technical data

### Dimensions

Length (b)	260 mm
Blade width	0 mm

### Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C
Degree of protection	IP65

### General

# Voltage tester - DUSPOL EXPERT - 1209091

## Technical data

### General

Color	black
Power supply	2 x micro battery 1.5 V, LR03, AAA
Measuring category	CAT IV 600 V / CAT III 1000V
Test certificate	EN/IEC 61243-3 (VDE 0682 Part 401)
Display scope	12 V, 24 V, 50 V, 120 V, 230 V, 400 V, 690 V, 1000 V LED diode display
Phase-sequence indicator	LCD (symbol "R")
Phase display	LCD (symbol "R")
Polarity display	LED (symbol "+/-")
Measuring point lighting	LED
Innenwiderstand_Messkreis	220 kΩ
Innenwiderstand_Lastkreis	3.7 kΩ
Minimum voltage	12 V DC
Max. voltage	1000 V DC
Minimum voltage	12 V AC
Max. voltage	1000 V AC

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

## Approvals


### Approvals

#### Approvals

VDE Zeichengenehmigung / EAC

#### Ex Approvals

### Approval details

VDE Zeichengenehmigung		<a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a>	40038336
------------------------	---	---	----------

## Voltage tester - DUSPOL EXPERT - 1209091

### Approvals

EAC



EAC-Zulassung

Phoenix Contact 2019 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>