

Programming adapter - TWN4 MIFARE NFC USB ADAPTER - 2909681


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Near Field Communication (NFC) programming adapter with USB interface for the wireless configuration of NFC-capable products from PHOENIX CONTACT with software. No separate USB driver is required.

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 5 5 6 2 6 3 7 0 5 6 9
GTIN	4055626370569

Technical data

Input data

Input voltage range	4.3 V ... 5.5 V
---------------------	-----------------

Ambient conditions

Ambient temperature (operation)	25 °C ... 80 °C
Ambient temperature (storage/transport)	-45 °C ... 85 °C
Max. permissible relative humidity (operation)	95 %

Dimensions

Width	56 mm
Height	18 mm
Depth	88 mm

Standards and Regulations

NFC standard	ISO 14443A
	ISO 15693

Programming adapter - TWN4 MIFARE NFC USB ADAPTER - 2909681

Classifications

eCl@ss

eCl@ss 10.0.1	27371392
eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379201
eCl@ss 8.0	27379201
eCl@ss 9.0	27379201

ETIM

ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002498

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-D-03506
-----	---	-------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>