

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component connector, with 47 kOhm resistance for wire-break monitoring, pitch: 5.2 mm, depth: 34.8 mm, width: 4.1 mm, height: 8.9 mm, number of positions: 2, color: black

Your advantages

- The component connector can easily plug into the bridge shaft of two adjacent CLIPLINE complete terminal blocks with a 5.1 mm pitch.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3032447 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z3X |
| GTIN | 4046356981606 |
| Weight per piece (including packing) | 1.45 g |
| Weight per piece (excluding packing) | 1.45 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Technical data

Notes

| | |
|---------|--|
| General | Can be used between two neighboring CLIPLINE complete terminal blocks with 2.5 mm ² conductor cross-section |
|---------|--|

Product properties

| | |
|---------------------|-------------------------------|
| Product type | Component plug terminal block |
| Number of positions | 2 |
| Pitch | 5.2 mm |

Dimensions

| | |
|--------|---------|
| Width | 4.1 mm |
| Height | 8.9 mm |
| Depth | 34.8 mm |
| Pitch | 5.2 mm |

Material specifications

| | |
|----------|------------------|
| Color | black (RAL 9005) |
| Material | PA |

Electrical tests

Surge voltage test

| | |
|-----------------------|-------------|
| Test voltage setpoint | 9.8 kV |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 2 kV |
| Result | Test passed |

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250305 |
| ECLASS-15.0 | 27250305 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002018 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

P-CO 2-5 R47K - Component connector



3032447

<https://www.phoenixcontact.com/us/products/3032447>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.63 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com